



# G Series - Short Momentary Contact Single Push Button Operator- Green Button With "Start"/"Stop" Nameplate - 1NO Contact Rating

By Killark  
Catalog # [GO21-GZ1B](#)

Killark GO SERIES Operators are a component use in conjunction with a Hazardous Location enclosure to provide control solutions in for; START/STOP Motor Functions, LED Pilot Light Indications and more. Utilized in Class 1 Division 1 & 2, Class 1 Zone 1 & 2 areas for indoor and outdoor use. UL Listed and CSA Certified.

## Features

- 
- 
- 
- 

## General

Action	Momentary
Actuator	Single Pushbutton
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Catalog Number	GO21-GZ1B
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	1
Series	GO
UPC	783936222745

## Dimensions

Dimensions	6.75 in x 2.25 in x 2 in
Gross Weight with Packaging	0.49
Height	2 in
Length	6.75 in
Width	2.25 in

## Electrical Ratings

Amperage Rating	10 A
Contact Rating	60A INRUSH @ 120 VAC; 30A INRUSH @ 240 VAC; 15A INRUSH @ 480 VAC; 12A INRUSH @ 600 VAC; 0.55A INRUSH @ 125 VDC; 0.275A INRUSH @ 250 VDC; 6A



\*Representative Image

BREAKING @ 120 VAC; 3A
BREAKING @ 240 VAC; 1.5A
BREAKING @ 480 VAC; 1.2A
BREAKING @ 600 VAC; 0.55A
BREAKING @ 125 VDC; 0.275A
BREAKING @ 250 VDC; 10A
CARRYING @ 120 VAC; 10A
CARRYING @ 240 VAC; 10A
CARRYING @ 480 VAC; 10A
CARRYING @ 600 VAC; 2.5A
CARRYING @ 125 VDC; 2.5A
CARRYING @ 250 VDC.
50/60 Hz

Frequency Rating

## Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups C, D</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
UL File Number	E12379

## Product Assets

- [Certifications - GO Series Controls UL Certification](#)
- [Certifications - GO Series Operators CSA Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL\\_GO21 Single Pushbutton Operators \(Short\) IOM\\_K0330](#)
- [Specifications - G Series Push Buttons Specification Sheet](#)
- [Specifications - GO21-GZ1B Specification Sheet French](#)
- [Specifications - GO21GZ1B Specification Sheet English](#)