



G Series - Short Momentary Contact Double Push Button Operator- Green And Red Buttons With "Start - Stop"/Blank Nameplate - 1NO/1NCcontact Rating

By Killark
Catalog # [GO22-GR12D](#)



*Representative Image

Killark GO SERIES Operators are a component use in conjunction with a Hazardous Location enclosure to provide control solutions in for; START/STOP Motor Functions, LED Pilot Light Indications and more. Utilized in Class 1 Division 1 & 2, Class 1 Zone 1 & 2 areas for indoor and outdoor use. UL Listed and CSA Certified.

Features

-
-
-
-

General

Action	Momentary
Actuator	Double Pushbutton
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Catalog Number	GO22-GR12D
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	2
Series	GO
UPC	783936222882

Dimensions

Dimensions	6.31 in x 2.25 in x 1.25 in
Gross Weight with Packaging	0.4
Height	1.25 in
Length	6.31 in
Width	2.25 in

Electrical Ratings

Amperage Rating	10 A
Contact Rating	60A INRUSH @ 120 VAC; 30A INRUSH @ 240 VAC; 15A INRUSH @ 480 VAC; 12A INRUSH @ 600 VAC; 0.55A INRUSH @ 125 VDC; 0.275A

INRUSH @ 250 VDC; 6A
BREAKING @ 120 VAC; 3A
BREAKING @ 240 VAC; 1.5A
BREAKING @ 480 VAC; 1.2A
BREAKING @ 600 VAC; 0.55A
BREAKING @ 125 VDC; 0.275A
BREAKING @ 250 VDC; 10A
CARRYING @ 120 VAC; 10A
CARRYING @ 240 VAC; 10A
CARRYING @ 480 VAC; 10A
CARRYING @ 600 VAC; 2.5A
CARRYING @ 125 VDC; 2.5A
CARRYING @ 250 VDC.

Frequency Rating

50/60 Hz

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
UL File Number	E12379

Product Assets

- [Certifications - GO Series Controls UL Certification](#)
- [Certifications - GO Series Operators CSA Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - GO22GR12D Specification Sheet English](#)
- [Specifications - G Series Push Buttons Specification Sheet](#)
- [Specifications - GO22-GR12D Specification Sheet French](#)