



# G Series - Short Momentary Contact Double Push Button Operator- Green And Red Buttons With "Start - Stop"/Blank Nameplate - 2NO/2NCcontact Rating

By Killark  
Catalog # GO22-GR33D



\*Representative Image

G Series - Aluminum Short Momentary Contact Double Push Button Operator- Green And Red Buttons With "Start - Stop"/Blank Nameplate - 2NO/2NCcontact Rating.

## Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

## General

Action	Momentary
Actuator	Double Pushbutton
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Application	
Catalog Number	GO22-GR33D
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	2
Series	GO
Type	
UPC	783936222905

## Dimensions

Dimensions	6.75 in x 2.25 in x 2 in
Gross Weight with Packaging	0.65
Height	2 in
Length	6.75 in
Width	2.25 in

## Electrical Ratings

Amperage Rating	10 A
Contact Rating	60A INRUSH @ 120 VAC; 30A INRUSH @ 240 VAC; 15A INRUSH @ 480 VAC; 12A INRUSH @ 600 VAC; 0.55A INRUSH @ 125 VDC; 0.275A INRUSH @ 250 VDC; 6A BREAKING @ 120 VAC; 3A BREAKING @ 240 VAC; 1.5A BREAKING @ 480 VAC; 1.2A BREAKING @ 600 VAC; 0.55A BREAKING @ 125 VDC; 0.275A BREAKING @ 250 VDC; 10A CARRYING @ 120 VAC; 10A CARRYING @ 240 VAC; 10A CARRYING @ 480 VAC; 10A CARRYING @ 600 VAC; 2.5A CARRYING @ 125 VDC; 2.5A CARRYING @ 250 VDC.
Frequency Rating	50/60 Hz

## Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D  Class II, Divisions 1 & 2, Groups E, F, G  Class III, Divisions 1 & 2
UL File Number	E12379

## Product Assets

- [Certifications - GO Series Controls UL Certification](#)
- [Certifications - GO Series Operators CSA Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
KILL\_CA-GO22GR33D-SPEC-EN | REV 6/2024