



# G Series -Long 120V Pilot Light Operator - Red Lens With Blank Nameplate

By Killark  
Catalog # [GOB3-R23C N34](#)



\*Representative Image

Killark GO SERIES Operators are a component use in conjunction with a Hazardous Location enclosure to provide control solutions in for; START/STOP Motor Functions, LED Pilot Light Indications and more. Utilized in Class 1 Division 1 & 2, Class 1 Zone 1 & 2 areas for indoor and outdoor use. UL Listed and CSA Certified.

### General

Actuator	Pilot Light
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Catalog Number	GOB3-R23C N34
EU RoHS Indicator	Contact Manufacturer
Operating Cycles	10,000 hrs
Series	GO
UPC	783936997193

### Dimensions

Depth	2-3/4
Dimensions	6.31 in x 2.25 in x 1.25 in
Gross Weight with Packaging	0.5
Height	1.25 in
Length	6.31 in
Width	2.25 in

### Electrical Ratings

Amperage Rating	0.025 A
Frequency Rating	50/60 Hz

Voltage Rating	250 V
----------------	-------

### Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none"><li>Class I, Divisions 1 &amp; 2, Groups B, C, D</li><li>Class I, Zones 1 &amp; 2, Groups IIB, IIA</li><li>Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>Class III, Divisions 1 &amp; 2</li></ul>
Nema Rating	3, 4, 4X
UL File Number	E12379

### Product Assets

- [Certifications - GO Series Operators CSA Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - G Series Pilot Lights Specification Sheet](#)
- [Specifications - GOB3R23CN34 Specification Sheet English](#)
- [Specifications - GOB3-R23C N34 Specification Sheet French](#)