

## GOB4-A233CN34CN

By Killark

Catalog # [GOB4-A233CN34CN](#)

G Series - Aluminum ATEX Certified Long 120V Illuminated Push Button (Push To Test Pilot Light) Operator - Amber Lens With Blank Nameplate -1NO/1NC Contact Rating.



### Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

### General

Action	Momentary
Actuator	Pilot Light and Momentary Pushbutton
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Application	
Catalog Number	GOB4-A233CN34CN
Color	Amber
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	1
Operating Cycles	10,000 operations
Series	GO
Type	
UPC	783936225623

### Dimensions

Depth	4
Gross Weight with Packaging	1

### Electrical Ratings

Amperage Rating	10 A
Contact Rating	NEMA A600 - 7200 VA (make), 720 VA (break), 10A cont. @ 600V AC (thermal); NEMA Q300 - 69 VA (make & break), 2.5A cont. @ 250V DC (thermal).
Frequency Rating	50/60 Hz
Voltage Rating	250 V

### Certifications And Compliance

ATEX File Number	03ATEX 1203 U
CSA File Number	LR11714
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups B, C, D Class I, Zones 1 & 2, Groups IIB, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X
UL File Number	E12379

### Product Assets

- [Certifications - GO Series Pilot Lights ATEX Certificate](#)
- [Certifications - GO Series Pilotlights Attestation of Conformity](#)
- [Certifications - GO Series Pilot Lights UL Certification](#)
- [Certifications - GO Series Operators CSA Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
KILL\_CA-GOB4A233CN34CN-SPEC-EN | REV 6/2024