



G Series -Extended 120V Illuminated Push Button (Push To Test Pilot Light) Operator - Red Lens With Blank Nameplate - Without Contacts

By Killark
Catalog # [GOL4R](#)



*Representative Image

Killark GO SERIES Operators are a component use in conjunction with a Hazardous Location enclosure to provide control solutions in for; START/STOP Motor Functions, LED Pilot Light Indications and more. Utilized in Class 1 Division 1 & 2, Class 1 Zone 1 & 2 areas for indoor and outdoor use. UL Listed and CSA Certified.

Features

-
-
-
-

General

Action	Momentary
Actuator	Pilot Light and Momentary Pushbutton
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Catalog Number	GOL4R
Color	Red
EU RoHS Indicator	Contact Manufacturer
Operating Cycles	10,000 hrs
Series	GO
UPC	783936226330

Dimensions

Depth	4
Dimensions	8.5 in x 3.75 in x 3.75 in
Gross Weight with Packaging	1
Height	3.75 in
Length	8.5 in
Width	3.75 in

Electrical Ratings

Amperage Rating	10 A
Frequency Rating	50/60 Hz
Voltage Rating	250 V

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups B, C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X
UL File Number	E12379

Product Assets

- [Certifications - GO Series Pilot Lights UL Certification](#)
- [Certifications - GO Series Operators CSA Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - G Series Pilot Lights Specification Sheet](#)
- [Specifications - GOL4R Specification Sheet English](#)
- [Specifications - GOL4R Specification Sheet French](#)