



GR Series, Blank Cover GRB,, Cast Aluminum Type 4, Screw Cover Enclosure

By Killark
Catalog # [GRB-BC](#)

GR Series, Blank Cover GRB Type 4,Screw Cover Enclosure

Features

- Threaded blank screw covers provide easy access to interior
- High strength, lighter weight, corrosion resistant copper free cast aluminum construction
- Cover o-ring, Nitrile (BUNA-N) material, supplied standard for a Type 4X rating
- Electrostatically applied gray powder epoxy/polyester finish on exterior of covers.

General

Catalog Number	GRB-BC
Cover Type	Threaded
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Series	GR Enclosures
UPC	783936230207

Dimensions

Dimensions	4.625 in x 1.625 in x 4.625 in
Gross Weight with Packaging	1
Height	4.625 in
Length	4.625 in
Width	1.625 in

Certifications And Compliance



*Representative Image

CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups B, C, D• Class I, Zones 1 & 2, Groups IIB+H2, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X
UL File Number	E10514 / E83696

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Certifications - GR Series Enclosures ATEX Certificate](#)
- [Certifications - GR Series Enclosures IECEx Certification](#)
- [Certifications - GR Series Controls IECEx Certification](#)
- [Certifications - GR Series Enclosures CSA Certification](#)
- [Certifications - GR Series Controllers ATEX Certificate](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - GR Series Drill & Tap IOM K0986](#)
- [Specifications - GRBBC Specification Sheet English](#)
- [Specifications - GR Series Threaded Enclosures Specification Sheet](#)
- [Specifications - GRB-BC Specification Sheet French](#)



A Hubbell brand