



By Killark
Catalog # GRE-BC

GR, Blank Cover GRE Type 4,Screw Cover Enclosure



Features

- Threaded blank screw covers provide easy access to interior
- High strength, lighter weight, corrosion resistant copper free cast aluminum construction
- Cover o-ring, Nitrile (BUNA-N) material, supplied standard for a Type 4X rating
- Electrostatically applied gray powder epoxy/polyester finish on exterior of covers.

Application

For use with GRE Series enclosures.

Specifications

EU RoHS Indicator	Contact Manufacturer
CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups B, C, D;Class I, Zones 1 & 2, Groups IIB+H2, IIA;Class II, Divisions 1 & 2, Groups E, F, G;Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X

UL File NumberE10514 / E83696

Dimensions

Length	5.25 in
Gross Weight with Packaging	1.5
Width	2.188 in
Height	5.25 in
Dimensions	5.25 in x 2.188 in x 5.25 in

General

Color	Gray
Type	Blank Cover
Material	Copper-free aluminum
UPC	783936231143

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page \[English\]](#)
[Installation Manual \[English\]](#)