



GR Series, Blank Cover GRL, Cast Aluminum Type 4, Screw Cover Enclosure

By Killark
Catalog # GRL-BC

GR Series, Blank Cover GRL Type 4,Screw Cover Enclosure.



*Representative Image

Features

- Threaded blank screw covers provide easy access to interior
- High strength, lighter weight, corrosion resistant copper free cast aluminum construction
- Cover o-ring, Nitrile (BUNA-N) material, supplied standard for a Type 4X rating
- Electrostatically applied gray powder epoxy/polyester finish on exterior of covers.
- Les couvercles de vis vierges filetés offrent un accès facile à l'intérieur
- Construction en aluminium coulé sans cuivre haute résistance, plus léger et résistant à la corrosion
- Joint torique du couvercle, matériau nitrile (BUNA-N), fourni en standard pour une classification de type 4X
- Finition époxy/polyester en poudre grise à l'extérieur des couvercles

General

Application	
Catalog Number	GRL-BC
Color	
Cover Type	Threaded
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Series	GR Enclosures
Type	
UPC	783936232928

Dimensions

Dimensions	10.31 in x 8.38 in x 4.13 in
Gross Weight with Packaging	3.4
Height	4.13 in
Length	10.31 in
Width	8.38 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups B, C, D Class I, Zones 1 & 2, Groups IIB+H2, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
UL File Number	E10514 / E83696

Product Assets

- [Certifications - GR Series Controllers ATEX Certificate](#)
- [Certifications - GR Series Enclosures ATEX Certificate](#)
- [Certifications - GR Series Controls IECEx Certification](#)
- [Certifications - GR Series Enclosures IECEx Certification](#)
- [Certifications - GR Series Enclosures CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - GR Series Drill & Tap IOM K0986](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-GRLBC-SPEC-EN | REV 6/2024