



GR Series, 6 X 6 X 12.25, Class I, II, III, BCDEFG, Cast Aluminum, Type 4, Viewing Lens Screw Cover Enclosure

By Killark
Catalog # [GRM-375L](#)

GR Series, 6 X 6 X 12.25, Class I, II, III, BCDEFG, Cast Aluminum, Type 4, Viewing Lens Screw Cover Enclosure.



*Representative Image

Features

- Cast mounting lugs are standard on all boxes.
- Internal ground screw supplied on all boxes.
- Electrostatically applied gray powder epoxy/polyester finish on exterior of box and cover.
- Mounting pans are available.
- Conduit and device openings factory or field installed.

General

Application	
Catalog Number	GRM-375L
Color	
Cover Type	Threaded
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Series	GR Enclosures
Type	
UPC	783936233468

Dimensions

Dimensions	10.25 in x 8.5 in x 7.5 in
Gross Weight with Packaging	14.4
Height	7.5 in
Length	10.25 in
Width	8.5 in

Certifications And Compliance

ATEX File Number	PTB 02 ATEX 1071U / PTB 02 ATEX 1072
CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups B, C, D Class I, Zones 1 & 2, Groups IIB+H2, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
IECEX File Number	IEC E x 05.0029U / IEC E x 05.0028
UL File Number	E10514 / E83696

Product Assets

- [3D Models - GRM-375 3D File](#)
- [Certifications - GR Series Enclosures IECEx Certification](#)
- [Certifications - GR Series Enclosures UL Certificate](#)
- [Certifications - GR Series Enclosures Attestation of Conformity](#)
- [Certifications - GR Series Enclosures CSA Certification](#)
- [Certifications - GR Series Controllers ATEX Certificate](#)
- [Certifications - GR Series Enclosures ATEX Certificate](#)
- [Certifications - GR Series Controls IECEx Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - GRM-375 Engineering Drawing](#)
- [Installation Manuals - GR Series Drill & Tap IOM K0986](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-GRM375L-SPEC-EN | REV 6/2024