



# GR Series, 6 X 6 X 4.18, Class I, II, III, BCDEFG, Cast Aluminum, Type 4, Without Screw Cover Enclosure

By Killark  
Catalog # [GRMB](#)

GR Series, 6 X 6 X 4.18, Class I, II, III, BCDEFG, Cast Aluminum, Type 4, Without Screw Cover Enclosure

## Features

- Compact rectangular enclosures with threaded screw covers provide easy access to interior.
- High strength, lighter weight, corrosion resistant copper free cast aluminum construction.
- Available with a flat blank or dome covers.
- Cover o-ring, Nitrile (BUNA-N) material, supplied standard supplied standard for a Type 4X rating.
- Cast mounting lugs are standard on all boxes.
- Internal ground screw supplied on all boxes.
- Electrostatically applied gray powder epoxy/polyester finish on exterior of box and cover.
- Mounting pans are available.
- Conduit and device openings factory or field installed.

## General

Catalog Number	GRMB
Cover Type	Threaded
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Series	GR Enclosures
UPC	783936228020

## Dimensions

Dimensions	9.75 in x 8.5 in x 7.625 in
Gross Weight with Packaging	12.7
Height	7.625 in
Length	9.75 in
Width	8.5 in



\*Representative Image

## Certifications And Compliance

ATEX File Number	PTB 02 ATEX 1071U / PTB 02 ATEX 1072
CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups B, C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB+H2, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
IECEX File Number	IEC E x 05.0029U / IEC E x 05.0028
UL File Number	E10514 / E83696

## Product Assets

- [Certifications - GR Series Enclosures ATEX Certificate](#)
- [Certifications - GR Series Enclosures CSA Certification](#)
- [Certifications - GR Series Controllers ATEX Certificate](#)
- [Certifications - GR Series Enclosures IECEX Certification](#)
- [Certifications - GR Series Controls IECEX Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - GRMB Engineering Drawing](#)
- [Installation Manuals - KIL\\_GR Series Threaded Enclosures IOM\\_K1144](#)
- [Installation Manuals - GR Series Drill & Tap IOM K0986](#)
- [Specifications - GRMB Specification Sheet English](#)
- [Specifications - GR Series Threaded Enclosures Specification Sheet](#)
- [Specifications - GRMB Specification Sheet French](#)



A Hubbell brand