

GUF-1

By Killark
Catalog # [GUF-1](#)

½" Union, Female to Female



*Representative Image

Features

- Threaded for rigid conduit or IMC
- Tapered threads (NPT)
- Strong and durable construction

Application

Permits removal of equipment without turning or removal of conduit.

General

Catalog Number	GUF-1
Color	Silver
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	GUF
Type	Female to Female Union
UPC	783936270012

Dimensions

Dimensions	2 in x 2 in x 2 in
Gross Weight with Packaging	0.12
Height	2 in
Hub Size	1/2"

Length	2 in
Weight	0.12 lb
Width	2 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups A, B, C, D• Class I, Zones 1 & 2, Groups IIC, IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
UL File Number	E10514

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Certifications - GUF/GUM Series Unions UL Certification](#)
[Certifications - GUF/GUM Series Unions CSA Certification](#)
[Customer Notices - Prop 65 Notice](#)
[Specifications - GUF1 Specification Sheet English](#)
[Specifications - GUF-1 Specification Sheet French](#)
[Specifications - GUF/GUM & UNF/UNY Series Unions Specification Sheet](#)