



GUM-O-EX - 4" Union, Aluminum, Male to Female, Quad Listed

By Killark

Catalog # [GUM-O-EX](#)

4" Union, Aluminum, Male to Female, Quad Listed.



*Representative Image

Features

- Threaded for rigid conduit or IMC
- Tapered threads (NPT)
- Strong and durable construction
- Certified QUAD LISTED

General

Application	
Catalog Number	GUM-O-EX
Color	Silver
	Argent
EU RoHS Indicator	Contact Manufacturer
Finish Type	Naturel
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	GUM
Type	
UPC	783936071855

Dimensions

Gross Weight with Packaging	4
Hub Size	4"

Certifications And Compliance

ATEX File Number	ITS09ATEX16417U
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D
	Class I, Zones 1 & 2, Groups IIB, IIA
	Class II, Divisions 1 & 2, Groups E, F, G
	Class III, Divisions 1 & 2
IECEX File Number	IECEXITS09.0024U

Product Assets

- [Certifications - Elbows & Union UKCA Certificate](#)
- [Certifications - Elbows & Union ATEX Certificate](#)
- [Certifications - Elbows & Unions IECEx Certification](#)
- [Certifications - GUF/GUM Series Unions CSA Certification](#)
- [Certifications - EX Series Elbows & Unions Declaration of Conformity](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - ATEX Elbows & Unions IOM K1435](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-GUM0EX-SPEC-EN | REV 6/2024