

## GUM-O-EX - Raccord 4", aluminium, mâle-femelle, quadruple homologué

Par Killark

No de catalogue [GUM-O-EX](#)

Raccord 4", aluminium, mâle à femelle, répertorié Quad.



\*Image représentative

### Caractéristiques

- Fileté pour conduit rigide ou IMC
- Filetage conique (NPT)
- Construction solide et durable
- Certifié QUAD LISTED

### Général

Numéro de catalogue	GUM-O-EX
Couleur	<ul style="list-style-type: none"><li>• Argent</li><li>• Argent</li></ul>
Indicateur RoHS de l'UE	Contacter le fabricant
Type de finition	Naturel
Matériau	Sans aluminium ni cuivre (moins de 4/10 de 1 %)
Série	GUM
Type	
CUP	783936071855

### Dimensions

Poids brut avec emballage	4
Taille du moyeu	4"

### Certifications et conformité

Numéro de dossier ATEX	ITS09ATEX16417U
Cote(s) de dangerosité	<ul style="list-style-type: none"><li>• Classe I, divisions 1 et 2, groupes C et D</li><li>• Classe I, zones 1 et 2, groupes IIB, IIA</li><li>• Classe II, divisions 1 et 2, groupes E, F, G</li><li>• Classe III, divisions 1 et 2</li></ul>
Numéro de dossier IECEx	IECExITS09.0024U

### Documentation

- [Avis aux clients - Prop 65 Notice](#)
- [Certifications - Elbows & Union UKCA Certificate](#)
- [Certifications - Elbows & Union ATEX Certificate](#)
- [Certifications - Elbows & Unions IECEx Certification](#)
- [Certifications - GUF/GUM Series Unions CSA Certification](#)
- [Certifications - EX Series Elbows & Unions Declaration of Conformity](#)
- [Manuels d'installation - ATEX Elbows & Unions IOM K1435](#)
- [Spécifications - GUM-O-EX](#)
- [Spécifications - GUF/GUM & UNF/UNY Series Unions](#)
- [Specification Sheet](#)
- [Spécifications - GUM-O-EX](#)