



GZ Series - PilotLight, Amber with Lamp Holder & Lamp 120V AC/DC - Long Length 40mm, 3/4 NPSM

By Killark
Catalog # [GZB3-A23](#)



Pilot Light, Amber with Lamp Holder & Lamp 120V AC/DC - Long Length 40mm, 3/4 NPSM

Features

-
-
-
-

General

Catalog Number	GZB3-A23
Color	Amber
EU RoHS Indicator	Contact Manufacturer
Series	GZ
UPC	783936175720

Dimensions

Dimensions	4.2 in x 1.8 in x 1.8 in
Height	1.8 in
Length	4.2 in
Weight	0.25 lb
Width	1.8 in

Electrical Ratings

Amperage Rating	12 mA
Frequency Rating	50/60 Hz
Wattage	1.5 W

Certifications And Compliance

ATEX File Number	SIRA 19ATEX 1171 U
------------------	--------------------

Hazardous Rating(s)

- Class I, Divisions 1 & 2, Groups B, C, D
- Class II, Divisions 1 & 2, Groups E, F, G
- Class III, Divisions 1 & 2
- Zones 1 & 2
- Zones 21 & 22
- II 2 G Ex db IIC/IIB+H2Gb
- II 2 D Ex tb IIIC Db

IECEX File Number
Nema Rating
UL File Number

IECEX SIR 19.0054 U
Type 4X
E12379

Product Assets

- [3D Models - GZB3-A23 3D File](#)
- [Certifications - GZ Series IECEX Certificate](#)
- [Certifications - GZ Series Attestation of Conformity](#)
- [Certifications - GZ Series ATEX Certificate](#)
- [Certifications - GZ Series UL Certificate](#)
- [Engineering Drawing - GZ Series Dimensional Drawings](#)
- [Installation Manuals - GZ Series Actuators & Signal Devices](#)
- [Installation Manual K1506](#)
- [Sales Drawings - GZ Series Dimensional Drawings](#)
- [Specifications - GZB3A23 Specification Sheet English](#)
- [Specifications - GO Series To GZ Series Cross Reference](#)
- [Specifications - GZ Series Operators Specification Sheet](#)
- [Specifications - GZB3-A23 Specification Sheet French](#)
- [Video - GZ Operators](#)
- [Video - GZ Operators](#)