



HFX-265-152-EL-T8 - HFX430 Mod For HC

By Killark
Catalog # [HFX-265-152-EL-T8](#)

HFX430 Mod For HC

Features

- UL Listed and labeled for use inside paint spray booths and rooms
- 2' nominal compact models facilitate use in areas too small for nominal 4' models, or where the light must be confined
- Standard ballast is 120-277V at 50/60 Hz
- 0°F starting temperature
- Construction is strong lightweight corrosion resistant copper-free aluminum alloy, less than 4/10 of 1%
- All external hardware is corrosion resistant 316 stainless steel
- UL Listed externally fused ballast option protects fixture on line side of ballast, prevents ballast burnout
- Suitable for use in both indoor and outdoor wet locations
- Relamping easily accomplished by removing screw in cap and socket
- Factory sealed construction

General

Catalog Number	HFX-265-152-EL-T8
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	T8
Light Source	Linear Fluorescent
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Pendant
Optic Type	Glass Tubes



Series	HFX
UPC	783936041315

Dimensions

Hub Size	3/4"
----------	------

Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	120 VAC
Wattage	32 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
---------------------	--

Product Assets

- [Certifications - HFX Series Luminaires UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_HFX-265-x2](#)
- [Specifications - HFX-265-152-EL-T8 Specification Sheet French](#)
- [Specifications - HFX Series Fixtures Specification Sheet](#)
- [Specifications - HFX265152ELT8 Specification Sheet English](#)



A Hubbell brand