



# HFX-430-12 - HFX 40W Fluorescent 120V 2 Lamp

By Killark  
Catalog # [HFX-430-12](#)

HFX 40W Fluorescent 120V 2 Lamp

## Features

- UL Listed and labeled for use inside paint spray booths and rooms
- 2' nominal compact models facilitate use in areas too small for nominal 4' models, or where the light must be confined
- Standard ballast is 120-277V at 50/60 Hz
- 0°F starting temperature
- Construction is strong lightweight corrosion resistant copper-free aluminum alloy, less than 4/10 of 1%
- All external hardware is corrosion resistant 316 stainless steel
- UL Listed externally fused ballast option protects fixture on line side of ballast, prevents ballast burnout
- Suitable for use in both indoor and outdoor wet locations
- Relamping easily accomplished by removing screw in cap and socket
- Factory sealed construction

## General

Catalog Number	HFX-430-12
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	T12
Light Source	Linear Fluorescent
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Pendant
Optic Type	Glass Tubes



Series	HFX
UPC	783936287812

## Dimensions

Hub Size	3/4"
----------	------

## Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	120 VAC
Wattage	40 W

## Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
---------------------	--

## Product Assets

- [Certifications - HFX Series Luminaires UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL\\_HFX-430-x2](#)
- [Specifications - HFX43012 Specification Sheet English](#)
- [Specifications - HFX Series Fixtures Specification Sheet](#)
- [Specifications - HFX-430-12 Specification Sheet French](#)



A Hubbell brand