



HK Instrument Enclosure, 1" Dome Cover Class I, II, III, BCDEFG, UL/CSA/FM, Cast Aluminum, Type 4,

By Killark
Catalog # [HK1D](#)

HK Series, 1" Dome Cover Class I, II, III, BCDEFG, UL/CSA/FM, Cast Aluminum, Type 4, Instrument Enclosure.



*Representative Image

Features

- Threaded blank screw covers provide easy access to interior.
- High strength, lighter weight, corrosion resistant copper free cast aluminum construction.
- Cover o-ring, Nitrile (BUNA-N) material, supplied standard
- Electrostatically applied gray powder epoxy/polyester finish on exterior of covers.
- Covers have shrouded tamper resistant set screws as standard.

General

Application	
Catalog Number	HK1D
Color	Gray
	Gris
Cover Type	Threaded
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Series	HK
Type	
UPC	783936071527

Dimensions

Gross Weight with Packaging	1.28
-----------------------------	------

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups A(suffix GA) B, C, D
	Class I, Zones 1 & 2, Groups IIB+H2, IIA
	Class II, Divisions 1 & 2, Groups E, F, G
	Class III, Divisions 1 & 2
UL File Number	E83696

Product Assets

- [Certifications - HK Series Instrument Enclosures FM Certificate of Conformity](#)
- [Certifications - HK Series Terminal Enclosures UKCA Certificate](#)
- [Certifications - HK Series Enclosures UKCA Certificate](#)
- [Certifications - HK & HKBX Series CSA Certificate of Compliance](#)
- [Certifications - HK & HKBX Series Enclosures UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-HK1D-SPEC-EN | REV 6/2024