



HK Instrument Enclosure, 4" Dome Lens Cover 2-5/16 Viewing Class I, II, III, BCDEFG, UL/CSA/FM, Cast Aluminum, Type 4,

By Killark
Catalog # [HK4GLD](#)

HK Series, 4" Dome Lens Cover 2-5/16 Viewing Class I, II, III, BCDEFG, UL/CSA/FM, Cast Aluminum, Type 4, Instrument Enclosure.



*Representative Image

Features

- Threaded glass lens screw covers provide easy access to interior.
- High strength, lighter weight, corrosion resistant copper free cast aluminum construction.
- Glass lens made of tempered sode lime.
- Cover o-ring, Nitrile (BUNA-N) material, supplied standard
- Electrostatically applied gray powder epoxy/polyester finish on exterior of covers.
- Covers have shrouded tamper resistant setscrews as standard.

General

Application	
Catalog Number	HK4GLD
Color	Gray
	Gris
Cover Type	Threaded
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Series	HK
Type	
UPC	783936088372

Dimensions

Dimensions	6.625 in x 6 in x 4.375 in
Gross Weight with Packaging	4.47
Height	4.375 in
Length	6.625 in
Width	6 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups A(suffix GA) B, C, D
	Class I, Zones 1 & 2, Groups IIB+H2, IIA
	Class II, Divisions 1 & 2, Groups E, F, G
	Class III, Divisions 1 & 2

Product Assets

- [3D Models - HK4GLD 3D Model](#)
- [Certifications - HK Series Terminal Enclosures UKCA Certificate](#)
- [Certifications - HK Series Enclosures UKCA Certificate](#)
- [Certifications - HK Series Instrument Enclosures FM Certificate of Conformity](#)
- [Certifications - HK & HKBX Series CSA Certificate of Compliance](#)
- [Certifications - HK & HKBX Series Enclosures UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - HK4GLD Engineering Drawing](#)
- [Sales Drawings - HK4GLD Sales Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-HK4GLD-SPEC-EN | REV 6/2024