



HK Instrument Enclosure, 3-1/2 ID RD Body 3" DP, Class I, II, III, BCDEFG, UL/CSA/FM, Cast Aluminum, Type 4,

By Killark
Catalog # [HKB](#)

HK Series, 3-1/2 ID RD Body 3" DP, Class I, II, III, BCDEFG, UL/CSA/FM, Cast Aluminum, Type 4, Instrument Enclosure.



*Representative Image

Features

- Compact round body instrument enclosure for use with threaded screw cover to provide easy access to interior.
- High strength, lighter weight, corrosion resistant copper free cast aluminum construction.
- Available with a blank or lens cover, flat or domed.
- Cover o-ring, Nitrile (BUNA-N) material, supplied standard supplied standard for a Type 4X rating.
- Cast mounting lugs are standard on all boxes.
- Internal ground screw supplied on all boxes.
- Electrostatically applied gray powder epoxy/polyester finish on exterior of box.
- Offset feed-thru conduit openings (3/4" NPT) for maximum use of interior volume.
- Interior "X"-configuration mounting pad for instrument/device cast into the bottom of the box provided for flexibility.

Application

Instrumentation housed in HK Series enclosures typically used to measure, detect, monitor, transmit, and control industrial processes and systems. HK Series enclosures are suitable for a broad range of applications, meeting both domestic and international

General

Color	<ul style="list-style-type: none"> • Gray • Gris
Cover Type	Threaded
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Series	HK
Type	<ul style="list-style-type: none"> • Enclosure Only • Enclosure Only
UPC	783936295305

Dimensions

Dimensions	7.5 in x 5.75 in x 4.25 in
Gross Weight with Packaging	2.15
Height	4.25 in
Length	7.5 in
Width	5.75 in

Certifications and Compliance

ATEX File Number	DEMKO 01 ATEX 15742U
CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none"> • Class I, Divisions 1 & 2, Groups A(suffix GA) B, C, D • Class I, Zones 1 & 2, Groups IIB+H2, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
IECEX File Number	IECEX UL 14.0071U
UL File Number	E83696

Product Assets

- [Certifications - HK Series Instrument Enclosures FM Certificate of Conformity](#)
- [Certifications - HK & HKBX Series CSA Certificate of Compliance](#)
- [Certifications - HK & HKBX Series Enclosures Declaration of Conformity](#)
- [Certifications - HK & HKBX Series Enclosures With Terminal Blocks Declaration of Conformity](#)
- [Certifications - HK & HKBX Series Enclosures With Terminal Blocks ATEX Certificate](#)
- [Certifications - HK & HKBX Series Enclosure With Terminal Blocks ATEX Certificate \(Increased Safety\)](#)
- [Certifications - HK & HKBX Series Enclosures ATEX Certificate](#)
- [Certifications - HK & HKBX Series Enclosures UL Certification](#)
- [Certifications - HK & HKBX Series Enclosures with Terminal Blocks IECEX Certification \(Increased Safety\)](#)
- [Certifications - HK & HKBX Series Enclosures IECEX Certification](#)
- [Certifications - HK & HKBX Series Enclosures With Terminal Blocks IECEX Certification](#)
- [Certifications - HK Series Enclosures UKCA Certificate](#)
- [Certifications - HK Series Terminal Enclosures UKCA Certificate](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - HKB Series IOM K1232](#)

Related Products

- [HK2GLD - HK Instrument Enclosure, 2" Dome Lens Cover 2-5/16 Viewing Class I, II, III, BCDEFG, UL/CSA/FM, Cast Aluminum, Type 4,](#)
- [HK4D - HK Instrument Enclosure, 4" Dome Cover Class I, II, III, BCDEFG, UL/CSA/FM, Cast Aluminum, Type 4,](#)
- [HKGL - HK Instrument Enclosure, Flat Lens Cover 2-5/16 Viewing Class I, II, III, BCDEFG, UL/CSA/FM, Cast Aluminum,](#)

Viewing Class I, II, III, BCDEFG, UL/CSA/FM, Cast Aluminum,
Type 4
HFC - HK Instrument Enclosure, Flat Blank Cover Class I, II, III,
BCDEFG, UL/CSA/FM, Cast Aluminum, Type 4,
HK1D - HK Instrument Enclosure, 1" Dome Cover Class I, II, III,
BCDEFG, UL/CSA/FM, Cast Aluminum, Type 4,



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
KILL_CA-HKB-SPEC-EN | REV 1/2024