



## HKH1NC20PE

By Killark  
Catalog # HKH1NC20PE

HKH 20A Factory Sealed E-Stop - NC Contact - Panel Mount.



\*Representative Image

### General

Action	Momentary
Application	
Catalog Number	HKH1NC20PE
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	1
Operating Temperature Range Celcius	-40°C to 55°C
Series	HKH
UPC	783936124148

### Electrical Ratings

Amperage Rating	20 A
Frequency Rating	50/60 Hz
Voltage Rating	24-690 AC/DC V

### Certifications And Compliance

ATEX File Number	1202251U
Hazardous Rating(s)	Class I, Division 2, Groups A, B, C, D  Class I, Zones 1 & 2
IECEX File Number	12.0033U
UL File Number	E12379

### Logistics

Carton Quantity	20
-----------------	----

### Product Assets

[Certifications - HKH Contact Blocks Attestation of Conformity](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - HKH Series Contact Blocks IOM K1402](#)