

HKHPBMMMR

Par Killark

No de catalogue [HKHPBMMMR](#)

Bouton poussoir coup de poing momentané, rouge - 1NO/1NC
Contact Rating.



Caractéristiques

- Actionneur à utiliser avec les blocs de contact HKH sur rail Din et montés sur panneau pour les applications de type 3, 4, 4X, 12, 13 et IP66.

Général

Action	Momentané
Actionneur	Bouton-poussoir champignon
Numéro de catalogue	HKHPBMMMR
Indicateur RoHS de l'UE	Contacter le fabricant
Plage de température de fonctionnement Celcius	De -40°C à 55°C
Série	HKH
Type	
CUP	783936114064

Caractéristiques électriques

Fréquence nominale	50/60 Hz
--------------------	----------

Certifications et conformité

Numéro de dossier ATEX	1400U
Cote(s) de dangerosité	• Classe I, Division 2, Groupes A, B, C, D • Classe II, division 1, groupes E, F, G (Canada uniquement) • Classe II, division 2, groupes E, F, G • Classe III, divisions 1 et 2 • Zones 1 et 2 • Zones 21 et 22
Numéro de dossier IECEx	14.0104U
Nema Rating	4X
Numéro de dossier UL	E12379.

Logistique

Quantité de cartons	20
---------------------	----

Documentation

[Avis aux clients - Prop 65 Notice](#)
[Catalogues - Killark Catalog](#)
[Certifications - HKH Series Actuators & Pilot Lights ATEX Certificate](#)
[Certifications - HKH Series Actuators IECEx Certification](#)
[Certifications - HKH Series Actuators UL Certification](#)
[Manuels d'installation - HKH Series Actuators IOM K1444](#)
[Spécifications - HKHPBMMMR](#)
[Spécifications - HKHPBMMMR](#)
[Spécifications - HKH Series Actuators & Accessories](#)
[Specification Sheet](#)