



K1254 - 1 1/4" 45° Liquidtight Connector Non-Insulated

By Killark
Catalog # [K1254](#)

1 1/4" 45° Liquidtight Connector Non-Insulated



*Representative Image

Features

-
-
-
-

General

Catalog Number	K1254
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Finish Type	Zinc Plated
Insulation Type	Non-insulated
Material	Steel
Series	K Series
Style	45 Degree
UPC	783936991375

Dimensions

Hub Size	1-1/4"
----------	--------

Certifications And Compliance

CSA File Number	LR70873
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(B) (Class I, Division 2) or 502.10(A)(B) (Class II, Divisions 1 & 2) and 505.15(C) (Class I Zone 2).
UL File Number	E22699

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - Killark Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - K1254 Specification Sheet English](#)
- [Specifications - K Series Liquidtight Connectors Specification Sheet](#)
- [Specifications - K1254 Specification Sheet French](#)