



K350 - 3 1/2" Straight Liquidtight Connector Non-Insulated

By Killark
Catalog # [K350](#)

3 1/2" Straight Liquidtight Connector Non-Insulated



*Representative Image

Features

-
-
-
-

General

Catalog Number	K350
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Finish Type	Zinc Plated
Insulation Type	Non-insulated
Material	Iron, Malleable
Series	K Series
Style	Straight
UPC	783936998534

Dimensions

Hub Size 3-1/2"

Certifications And Compliance

CSA File Number	LR70873
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(B) (Class I, Division 2) or 502.10(A)(B) (Class II, Divisions 1 & 2) and 505.15(C) (Class I Zone 2).
UL File Number	E22699

Product Assets

- [Catalogs - Killark Catalog](#)
- [Specifications - K350 Specification Sheet English](#)
- [Specifications - K350 Specification Sheet French](#)
- [Specifications - K Series Liquidtight Connectors Specification Sheet](#)