



**KFS150SS - KFSS Series - Stainless Steel 150 Watt High Pressure Sodium Marine Floodlight (Lamp Not Included) - Quadri-Volt (120/208/240/277V) At 60Hz**

By Killark

Catalog # [KFS150SS](#)

KFSS Series - Stainless Steel 150 Watt High Pressure Sodium Marine Floodlight (Lamp Not Included) - Quadri-Volt (120/208/240/277V) At 60Hz



Features

- Type 316 Stainless Steel Housing. 16-gauge housing ensures low corrosion and long life, reducing maintenance costs
- Rugged quick-release 316 SS Lens Latches. No hardware seizing on disassembly saves maintenance time and money. Only tool needed is a screwdriver
- 316 SS Safety Lens Door Chains. Enables hands-free safe re-lamping
- 316 SS Mounting Yoke Reliable and safe installation
- Highly efficient photometrics and excellent asymmetrical distribution. Photometrics above 85%. Minimizes the number of required fixtures to deliver desired light levels. Saves in energy costs
- Hot-dipped Galvanized Steel Mounting Accessories. Corrosion resistant in marine and corrosive environments, assuring reliable installation
- 316 SS 3/4” Conduit Hub. Maintains grounding continuity. Watertightseal. Corrosion resistant
- Silicone Gasketed Lens Door Frame. Provides watertight seal, protecting interior from moisture and corrosives

Application

Offshore production platforms, refineries, offshore drilling rigs and barges, ocean-going vessels ports, wharfs, and jetties, waste water and sewage treatment facilities, any type of washdown, corrosive, abrasive, or dirty environment.

General

Catalog Number	KFS150SS
Color	Silver
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Mogul Base
Light Source	High Pressure Sodium
Material	Stainless Steel
Mounting Type	Trunnion
Number of Lamps	0

Optic Type	Glass Lens
Series	KFSS
Type	Stainless Steel High Pressure Sodium Floodlight
UPC	783936384221

Dimensions

Dimensions	22 in x 22 in x 11 in
Gross Weight with Packaging	49.2
Height	11 in
Length	22 in
Width	22 in

Electrical Ratings

Frequency Rating	60 Hz
Initial Lumens	16000
Voltage Rating	Quad - 120/277/347/480 VAC
Wattage	150 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2, Groups A, B, C, D</li><li>• Class I, Zone 2, Groups IIC, IIB, IIA</li><li>• Class II, Division 2, Groups F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
IP Rating	IP66

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KF-SS Stainless Steel Floodlight Luminaires IOM](#)
- [Photometry - KIL\\_KFS15xSS](#)
- [Specifications - KFSS Series Floodlight Specification Sheet](#)
- [Specifications - KFS150SS Specification Sheet French](#)
- [Specifications - KFS150SS Specification Sheet English](#)

