



KFS405-76 - KF Series - Aluminum 400 Watt High Pressure Sodium Marine Floodlight (Lamp Not Included) - 480V At 60Hz

By Killark
Catalog # [KFS405-76](#)



KF Series - Aluminum 400 Watt High Pressure Sodium Marine Floodlight (Lamp Not Included) - 480V At 60Hz

Features

- Rugged weathertight housing of copperfree aluminum with corrosion resistant bronze finish
- Wide beam distribution
- Thermal shock, impact-resistant lens
- Continuous silicone gasketing
- All external hardware is corrosion resistant including HubbellGard® ceramic coated screws
- Trunnion mounting-heavy gauge, hot dip galvanized steel mounting with stainless steel hardware
- 3/4" NPT entry on back lower left

General

Catalog Number	KFS405-76
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Mogul Base
Light Source	High Pressure Sodium
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Trunnion
Optic Type	Glass Lens
Series	KF

UPC

783936384177

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	480 VAC
Wattage	400 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"> • Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Division 2, Groups F, G • Class III, Divisions 1 & 2
---------------------	--

Product Assets

- [Certifications - KF Series CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_KFS40x-76](#)
- [Specifications - KFS405-76 Specification Sheet French](#)
- [Specifications - KFS40576 Specification Sheet English](#)
- [Specifications - KF Series Floodlights Specification Sheet](#)