



KP Series 20 Amp Plug - Includes 3 Grommets (Range 0.250-0.625) - 2P 3W Circuit - 115/230VAC At 60Hz - Rotate Right

By Killark
Catalog # [KP-20ABCSU37](#)



*Representative Image

KP Series - Aluminum 20 Amp Plug - Includes 3 Grommets (Range 0.250-0.625) - 2W 3P Circuit - 115/230VAC At 60Hz - Rotate Right

Features

-
-
-
-
-
-

General

Catalog Number	KP-20ABCSU37
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Number Of Poles	2
Receptacle Type	Delayed Action
Series	KP
UPC	783936042831

Electrical Ratings

Amperage Rating20 A

Conductor Related

Number Of Wires3

Certifications And Compliance

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB,IIA
Nema Rating	3, 4, 4X, 7(B, C, D), 9(F, G)

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KP/KR Series IOM K1066](#)
- [Specifications - KP-20ABCSU37 Specification Sheet French](#)
- [Specifications - KP20ABCSU37 Specification Sheet English](#)
- [Specifications - K Series Plug & Receptacle Specification Sheet](#)