



KP Series 30 Amp Plug - E Type - 3P 4W Circuit - Grommet Range 0.875- 1.125 Inch - 115/230VAC At 60Hz- Rotate Left

By Killark
Catalog # [KP-304E45SU38](#)



*Representative Image

KP Series - Aluminum 30 Amp Plug - E Type - 3W 4P Circuit -
Grommet Range 0.875-1.125 Inch - 115/230VAC At 60Hz- Rotate
Left.

Features

- Suitable where a connection is required for portable or movable equipment such as tools, motors, hand lights, etc.
- Solder Terminations for sure connection
- Copper free aluminum housing
- Delayed action contacts ensure safe interconnect
- Wide range of grommet openings
- Extra long grounding pin makes contact first and breaks contact last

General

Catalog Number	KP-304E45SU38
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Number Of Poles	3
Receptacle Type	Delayed Action
Series	KP
Type	
UPC	783936042930

Electrical Ratings

Amperage Rating	30 A
-----------------	------

Conductor Related

Number Of Wires	4
-----------------	---

Certifications And Compliance

Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D
	Class I, Zones 1 & 2, Groups IIB,IIA
Nema Rating	3, 4, 4X

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - KP/KR Series IOM K1066](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-KP304E45SU38-SPEC-EN | REV 6/2024