



KQS-250 ML - CELOX™ 250ml Killark Quick Sealing Compound With Four Static Mixing Nozzles

By Killark
Catalog # [KQS-250 ML](#)



CELOX™ Killark Quick Sealing Compound with 4 Static Mixing Nozzles - 250ml.

Features

- 250ml cartridge comes in a single barrel with a 2 chamber internal compartment that allows for more compact storing and use
- Two part epoxy resin is pushed through a patented static mixing wedge
- Each cartridge comes with 4 patented static mixing nozzles to form a perfect mix
- Cartridge dispensing guns and spare nozzles are available as ordering options

General

Series	Celox
Type	<ul style="list-style-type: none">• Sealing Compound• Sealing Compound
UPC	783936155319

Certifications and Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 1 & 2, Groups A, B, C, D• Class II, Division 1 & 2, Groups E, F, G• Class III, Division 1 & 2
---------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Product Assets

- [Brochures - Celox Gen II](#)
- [Brochures - EZ Seal Next Generation of Hazardous-Rated Seal Fittings](#)
- [Catalog Page - EZ Series The Next Generation of Vertical Seal Fittings](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - ENY Series & Sealing Compound CSA Certificate](#)
- [Installation Manuals - KQS Series Celox IOM K1513](#)
- [SDS - Killark Celox Part B Curing Agent SDS](#)
- [SDS - Killark Celox Part A Resin SDS](#)
- [Video - Celox Gen II](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
KILL_CA-KQS-250 ML-SPEC-EN | REV 1/2024