



KQS-250 ML - CELOX™ 250ml

Killark Quick Sealing Compound With Four Static Mixing Nozzles

By Killark
Catalog # [KQS-250 ML](#)

CELOX™ 250ml Killark Quick Sealing Compound With Four Static Mixing Nozzles



Features

-
-
-
-

General

Catalog Number	KQS-250 ML
EU RoHS Indicator	Contact Manufacturer
Series	Celox
UPC	783936155319

Certifications And Compliance

Hazardous Rating(s)	• Class I, Divison 1 & 2, Groups A, B, C, D • Class II, Division 1 & 2, Groups E, F, G
---------------------	--

- [Class III, Division 1 & 2](#)

Product Assets

- [Brochures - EZ Seal Next Generation of Hazardous-Rated Seal Fittings](#)
- [Brochures - Celox Gen II](#)
- [Catalog Page - EZ Series The Next Generation of Vertical Seal Fittings](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - ENY Series & Sealing Compound CSA Certificate](#)
- [Installation Manuals - KQS Series Celox IOM K1513](#)
- [SDS - Killark Celox Part B Curing Agent SDS](#)
- [SDS - Killark Celox Part A Resin SDS](#)
- [Specifications - KQS250ML Specification Sheet English](#)
- [Specifications - KQS-250 ML Specification Sheet French](#)
- [Specifications - Celox - Killark Quick Seal Specification Sheet](#)
- [Video - Celox Gen II](#)
- [Video - Celox Gen II](#)



A Hubbell brand