



KR Series - 20 Amp Receptacle With Feed-Thru Enclosure - 2P 3W Circuit - 115/230VAC At 60Hz - Hub Size 1/2 Inch

By Killark
Catalog # [KRS-218-120](#)

KR Series - Aluminum 20 Amp Receptacle With Feed-Thru Enclosure - 2W 3P Circuit - 115/230VAC At 60Hz - Hub Size 1/2 Inch

Features

-
-
-
-
-
-
-

General

Catalog Number	KRS-218-120
EU RoHS Indicator	Contact Manufacturer
Hub Pattern	Feed-Thru
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Number Of Poles	2
Receptacle Type	Delayed Action
Series	KR
UPC	783936391861

Dimensions

Hub Size	1/2"
----------	------

Electrical Ratings



*Representative Image

Amperage Rating	20 A
-----------------	------

Conductor Related

Number Of Wires	3
-----------------	---

Certifications And Compliance

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB,IIA
Nema Rating	3, 4, 4X, 7(B, C, D), 9(F, G)

Logistics

Carton Quantity	1
Factory Sealed	Factory Sealed

Product Assets

- [Catalogs - Killark Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - KRS218120 Specification Sheet English](#)
- [Specifications - KRS-218-120 Specification Sheet French](#)
- [Specifications - K Series Plug & Receptacle Specification Sheet](#)