



KWPL630 - 6,000 Lumen Range 120-277 Volt LED Wallpack Fixture

By Killark
Catalog # [KWPL630](#)

6,000 Lumen Range 120-277 Volt LED Wallpack Fixture

Features

- Aluminum with Bronze finish 1/2" hub on either side for conduit entry.
- Suitability for 55°C ambient, 90°C supply wire required.
- Lens thermal shock and impact resistant prismatic borosilicate glass.
- Two Hubbell Guard® Corrosion resistant hex head fasteners provide water-tight seal for door gasket.
- Optional factory installed photocells & fusing available.

General

Catalog Number	KWPL630
EU RoHS Indicator	Contact Manufacturer
Lumen Range	5,001-10,000 lm
Lumens	5636
Series	KWPL
UPC	783936143736

Dimensions



*Representative Image

Hub Size	1/2"
Weight	14 lb

Electrical Ratings

Voltage Rating	120-277 VAC
----------------	-------------

Certifications And Compliance

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA
Nema Rating	4X

Product Assets

- [Catalogs - Killark Catalog](#)
- [Photometry - KIL_KWPL630](#)
- [Specifications - KWPL Series LED Wallpack Specification Sheet](#)
- [Specifications - KWPL630 Specification Sheet English](#)
- [Specifications - KWPL630 Specification Sheet French](#)



A Hubbell brand