



KWPS100 - 100 Watt Quad Volt High Pressure Sodium Wallpack Fixture

By Killark
Catalog # [KWPS100](#)

100 Watt Quad Volt High Pressure Sodium Wallpack Fixture

Features

- Aluminum with Bronze finish 1/2" hub on either side for conduit entry.
- Mogul Porcelain Socket.
- Reflector is specular aluminum precision formed for optimal performance.
- Suitability for 55°C ambient, 90°C supply wire required.
- Lens thermal shock and impact resistant prismatic borosilicate glass.
- Full front access available for lamp or ballast service by hinging front door.
- Two Hubbell Guard® Corrosion resistant hex head fasteners provide water-tight seal for door gasket.
- Optional factory installed photocells, fusing, instant restrike, ballast protector, & lamps available.

General

Catalog Number	KWPS100
EU RoHS Indicator	Contact Manufacturer
Series	KWP
UPC	783936377087



*Representative Image

Dimensions

Hub Size	1/2"
Weight	24 lb

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	120-277 VAC
Wattage	100 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2, Groups A, B, C, D• Class I, Zone 2, Groups IIC, IIB, IIA
Nema Rating	4X

Product Assets

- [Specifications - KWPS100 Specification Sheet English](#)
- [Specifications - KWP Series Wallpacks Specification Sheet](#)
- [Specifications - KWPS100 Specification Sheet French](#)