

L27 - 3/4" L Hub, Iron Form 7 Conduit Body

By Killark
Catalog # [L27](#)

3/4" L Hub, Iron Form 7 Conduit Body



*Representative Image

Features

- Enhanced sealing capabilities neoprene sealing gaskets provide a NEMA 3 Seal.
- Suitable for wet locations when used with gaskets.
- High-quality sealing hardware 316 stainless steel cover screws and washers with neoprene gaskets.
- Innovative spring clip design for installation ease and repeat usage.
- For use with threaded rigid conduit steel or aluminum.
- Flat-back design for greater wiring capacity and mounting stability.

General

Catalog Number	L27
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	L
Material	Iron
Series	Duraloy 7
UPC	783936011516

Dimensions

Dimensions	6 in x 3 in x 2 in
Gross Weight with Packaging	1.08
Height	2 in
Hub Size	3/4"
Length	6 in

Width 3 in

Certifications And Compliance

CSA File Number	LR11852
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E3397

Logistics

Carton Quantity 5

Product Assets

3D Models - L27 3D Model
Catalogs - Killark Catalog
Certifications - Duraloy 7 UL Certificate of Compliance
Customer Notices - Prop 65 Notice
Engineering Drawing - L27 Engineering Drawing
Installation Manuals - KIL_Duraloy 7 Series Conduit Bodies IOM_K1430
Sales Drawings - L27 Sales Drawing
Specifications - Duraloy 7 Series Conduit Bodies Specification Sheet
Specifications - L27 Specification Sheet English
Specifications - L27 Specification Sheet French