



LB28 - 3/4" LB Hub, Iron Form 8 Conduit Body+E5732

By Killark
Catalog # [LB28](#)

3/4" LB Hub, Iron Form 8 Conduit Body+E5732



*Representative Image

Features

-
-
-
-
-

Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

General

Catalog Number	LB28
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	LB
Material	Iron
Series	Duraloy 8
Type	Conduit Body
UPC	783936481067

Dimensions

Dimensions	6 in x 2 in x 3 in
Gross Weight with Packaging	1.47
Height	3 in
Hub Size	3/4"

Length	6 in
Width	2 in

Certifications And Compliance

CSA File Number	LR11852
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E3397

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [3D Models - LB28 3D Model](#)
- [Catalogs - Killark Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - LB28 Engineering Drawing](#)
- [Sales Drawings - LB28 Sales Drawing](#)
- [Specifications - LB28 Specification Sheet English](#)
- [Specifications - LB28 Specification Sheet French](#)
- [Specifications - Conduit Fill Information](#)
- [Specifications - Duraloy 8 Series Conduit Bodies Specification Sheet](#)