



LR17 - 1/2" LR Hub, Iron Form 7 Conduit Body

By Killark
Catalog # [LR17](#)

1/2" LR Hub, Iron Form 7 Conduit Body



*Representative Image

Features

- Enhanced sealing capabilities neoprene sealing gaskets provide a NEMA 3 Seal.
- Suitable for wet locations when used with gaskets.
- High-quality sealing hardware 316 stainless steel cover screws and washers with neoprene gaskets.
- Innovative spring clip design for installation ease and repeat usage.
- For use with threaded rigid conduit steel or aluminum.
- Flat-back design for greater wiring capacity and mounting stability.

General

Catalog Number	LR17
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	LR
Material	Iron
Series	Duraloy 7
UPC	783936011202

Dimensions

Dimensions	5 in x 3 in x 2 in
Gross Weight with Packaging	0.9
Height	2 in
Hub Size	1/2"
Length	5 in

Width

3 in

Certifications And Compliance

CSA File Number	LR11852
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E3397

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [3D Models - LR17 3D Model](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - Duraloy 7 UL Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - LR17 Engineering Drawing](#)
- [Installation Manuals - KIL_Duraloy 7 Series Conduit Bodies IOM_K1430](#)
- [Sales Drawings - LR17 Sales Drawing](#)
- [Specifications - LR17 Specification Sheet English](#)
- [Specifications - Duraloy 7 Series Conduit Bodies Specification Sheet](#)
- [Specifications - LR17](#)



A Hubbell brand