



LZ2N54330 - LZ2S Series, Non-Metallic 54W Fluorescent Light Fixt (Three 4-Foot Lamps Not Incl), Double-Ended Lamp Type, 120-277V, 50/60Hz, Hub 3/4"

By Killark
Catalog # LZ2N54330



LZ2S Series - Non-Metallic 54 Watt Fluorescent Light Fixture
(Three 4-Foot Lamps Not Included) - Double-Ended Lamp Type
- 120-277V At 50/60Hz - Hub Size 3/4 Inch NPT

Features

-
-
-
-
-
-
-
-

General

Catalog Number	LZ2N54330
Color	White
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Lamp Type	T5
Material	Polyester, Fiberglass Reinforced
Mounting Type	- Pendant - Surface
Number of Lamps	0
Optic Type	Polycarbonate Lens - Clear
Reflector Type	Steel Reflector
Series	LZ2N
UPC	783936094274

Dimensions

Dimensions	4.5 in x 1 in x 6.5 in
Gross Weight with Packaging	24.5

Height	6.5 in
Length	4.5 in
Width	1 in

Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	120-277 VAC
Wattage	54 W

Certifications And Compliance

Hazardous Rating(s)	- Class I, Division 2, Groups A, B, C, D - Class I, Zone 2, Groups IIC, IIB, IIA - Class II, Divisions 1 & 2, Groups E, F, G - Class III, Divisions 1 & 2
IP Rating	IP66

Product Assets

- Customer Notices - Prop 65 Notice
- Installation Manuals - KIL_LZ2N Series Fluorescent Luminaires IOM_K1267
- Photometry - KIL_LZ2x543
- Specifications - LZ Series Fluorescent Fixtures Specification Sheet
- Specifications - LZ2N Series Non-Metallic Fluorescent Fixtures Specification Sheet
- Specifications - LZ2N54330 Specification Sheet French
- Specifications - LZ2N54330 Specification Sheet English