



## LZ2N55130 - LZ2S Series, Non-Metallic 55 W Fluorescent Light Fixture (One 2-Footlamp Not Included), Biaxial Lamp Type. 120-277V, 50/60Hz, Hub 3/4"

By Killark

Catalog # [LZ2N55130](#)

LZ2S Series - Non-Metallic 55 Watt Fluorescent Light Fixture  
(One 2-Footlamp Not Included) - Biaxial Lamp Type - 120-277V  
At 50/60Hz - Hubsize 3/4 Inch NPT

### Features

- Lexan® Clear Lens, impact resistant polycarbonate
- Housing-one piece fiberglass reinforced polyester, NEMA 4X & IP66 rated.
- Two 3/4" NTP aluminum hubs - one at each end (includes one 3/4" close-up plug and two 3/4" x 1/2" reducers for maximum user flexibility)
- Two 1/4"-20 aluminum bushings furnished in top of fixture for threaded rod
- 2' and 4' luminaries
- Lamp types Linear 17, 28, 32, 40, 44, 54, 60W Long compact 40, 55W (single ended)
- Electronic ballast standard
- World voltage (most models) 120 thru 277V, 50/60 Hz

### Application

LINEARLITE rugged non-metallic fluorescent fixtures are suitable for wet, harsh, and hazardous locations. Use where enclosed and gasketed fixtures are required to withstand exposure to moisture, dust, and corrosives. The LZ2N Series can also be used in Class I, Division 2, and Zone 2 hazardous vapors and in Class II areas where combustible dusts may exist. Typical areas used are in refineries, chemical plants, waste water and sewage treatment facilities, as well as in tunnels, food processing and coastal areas.

### General

Catalog Number	LZ2N55130
Color	White
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Lamp Type	Biaxial
Light Source	Linear Fluorescent
Material	Polyester, Fiberglass Reinforced
Mounting Type	<ul style="list-style-type: none"><li>• Pendant</li><li>• Surface</li></ul>
Number of Lamps	0
Optic Type	Polycarbonate Lens - Clear



Reflector Type  
Series  
Type

Steel Reflector  
LZ2N  
Non-Metallic Fluorescent  
Fixture  
783936395517

UPC

### Dimensions

Dimensions	8.25 in x 6.56 in x 31.5 in
Gross Weight with Packaging	11.8
Height	31.5 in
Length	8.25 in
Width	6.56 in

### Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	120-277 VAC
Wattage	55 W

### Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2, Groups A, B, C, D</li><li>• Class I, Zone 2, Groups IIC, IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
IP Rating	IP66

### Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - KIL\\_LZ2N Series Fluorescent Luminaires IOM\\_K1267](#)  
[Photometry - KIL\\_LZ2x551](#)  
[Specifications - LZ Series Fluorescent Fixtures Specification Sheet](#)  
[Specifications - LZ2N Series Non-Metallic Fluorescent Fixtures Specification Sheet](#)



A Hubbell brand