



LZ2S32230A - LZ2S Series,
Stainless Steel, 32 W Fluorescent Lt
Fixt (w/o Lamps), Double-Ended
Lamp Type, 120-277V, 50/60Hz,
Hub Size 3/4", AL Hubs

By Killark
Catalog # [LZ2S32230A](#)

LZ2S Series - Stainless Steel - 32 Watt Fluorescent Light Fixture
(Two 4-Foot Lamps Not Included) - Double-Ended Lamp Type -
120-277V At 50/60Hz -Hub Size 3/4 Inch NPT - Aluminum Hubs

Features

- NEMA 4X & IP66 rated stainless enclosure with Lexan® impact resistant polycarbonate lens.
- Two 3/4" NPT stainless hubs - one at each end (includes aluminum 3/4" close- up plug and two 3/4" x 1/2" reducers for maximum user flexibility).
- Two 1/4" - 20 stainless bushings furnished in top of fixture for threaded rod.

General

Catalog Number	LZ2S32230A
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Lamp Type	T8
Light Source	Linear Fluorescent
Material	Polyester, Fiberglass Reinforced
Mounting Type	• Pendant • Surface
Optic Type	Polycarbonate Lens - Clear
Series	LZ2S
UPC	783936074788

Electrical Ratings

Frequency Rating	50/60 Hz
------------------	----------



Voltage Rating	120-277 VAC
Wattage	32 W

Certifications And Compliance

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
IP Rating	IP66

Product Assets

- [Certifications - LZ2S Series CSA Cert](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_LZ2N Series Fluorescent Luminaires IOM_K1267](#)
- [Photometry - KIL_LZ2x322](#)
- [Specifications - LZ Series Fluorescent Fixtures Specification Sheet](#)
- [Specifications - LZ2S32230A Specification Sheet French](#)
- [Specifications - LZ2S32230A Specification Sheet English](#)
- [Specifications - LZ2S Series Fluorescent Fixtures Specification Sheet](#)