



# LZ2S44230 - LZ2S Series- Stainless Steel - 44W 120-277V - 4' 2-Lamp T-8 Electronic -20°F Start High Output Recessed Double Contact

By Killark  
Catalog # [LZ2S44230](#)

LZ2S Series- Stainless Steel - 44W 120-277V - 4' 2-Lamp T-8 Electronic -20°F Start High Output Recessed Double Contact

## Features

- NEMA 4X & IP66 rated stainless enclosure with Lexan® impact resistant polycarbonate lens.
- Two 3/4" NPT stainless hubs - one at each end (includes aluminum 3/4" close- up plug and two 3/4" x 1/2" reducers for maximum user flexibility).
- Two 1/4" - 20 stainless bushings furnished in top of fixture for threaded rod.

## General

|                   |                                                                             |
|-------------------|-----------------------------------------------------------------------------|
| Catalog Number    | LZ2S44230                                                                   |
| EU RoHS Indicator | Contact Manufacturer                                                        |
| Finish Type       | Natural                                                                     |
| Lamp Type         | T8                                                                          |
| Light Source      | Linear Fluorescent                                                          |
| Material          | Polyester, Fiberglass Reinforced                                            |
| Mounting Type     | <ul style="list-style-type: none"><li>• Pendant</li><li>• Surface</li></ul> |
| Optic Type        | Polycarbonate Lens - Clear                                                  |
| Series            | LZ2S                                                                        |
| UPC               | 783936395760                                                                |

## Electrical Ratings

|                  |          |
|------------------|----------|
| Frequency Rating | 50/60 Hz |
|------------------|----------|



|                |             |
|----------------|-------------|
| Voltage Rating | 120-277 VAC |
| Wattage        | 44 W        |

## Certifications And Compliance

|                     |                                                                                                                                                                                                                                           |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>• Class I, Division 2, Groups A, B, C, D</li><li>• Class I, Zone 2, Groups IIC, IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul> |
| IP Rating           | IP66                                                                                                                                                                                                                                      |

## Product Assets

- [Certifications - LZ2S Series CSA Cert](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL\\_LZ2N Series Fluorescent Luminaires IOM\\_K1267](#)
- [Photometry - KIL\\_LZ2x442](#)
- [Specifications - LZ Series Fluorescent Fixtures Specification Sheet](#)
- [Specifications - LZ2S44230 Specification Sheet English](#)
- [Specifications - LZ2S Series Fluorescent Fixtures Specification Sheet](#)
- [Specifications - LZ2S44230 Specification Sheet French](#)



A Hubbell brand