



MBF261-GGX2 - 26w Bi-Pin Fluorescent 120V 3/4" Ceiling Mount with Globe and Guard

By Killark
Catalog # [MBF261-GGX2](#)

26w Bi-Pin Fluorescent 120V 3/4" Ceiling Mount with Globe and Guard

Features

-
-
-
-
-
-
-
-
-
-

General

Catalog Number	MBF261-GGX2
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Bi Pin
Light Source	Compact Fluorescent
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Ceiling
Optic Type	Glass Globe - Fluted
Series	MB
UPC	783936405407

Dimensions

Hub Size	3/4"
----------	------



Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	120 VAC
Wattage	26 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2, Groups A, B, C, D• Class I, Zone 2, Groups IIC, IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
---------------------	---

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_MBF26x-G](#)
- [Photometry - KIL_MBF26x-G-S](#)
- [Photometry - KIL_MBF26x-G-A](#)
- [Specifications - MB Series Fluorescent Bi-Pin Specification Sheet](#)
- [Specifications - MBF261GGX2 Specification Sheet English](#)
- [Specifications - MBF261-GGX2 Specification Sheet French](#)