



# MBF391-R5GX3 - 39W Bi-Pin Fluorescent 120V 1" Ceiling Mount with Glass Refractor and Guard

By Killark  
Catalog # [MBF391-R5GX3](#)

39W Bi-Pin Fluorescent 120V 1" Ceiling Mount with Glass  
Refractor and Guard

### Features

- 
- 
- 
- 
- 
- 
- 
- 
- 
- 

### General

Catalog Number	MBF391-R5GX3
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Bi Pin
Light Source	Compact Fluorescent
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Ceiling
Optic Type	Glass Type V Refractor
Series	MB
UPC	783936405681

### Dimensions



Hub Size1"

### Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	120 VAC
Wattage	39 W

### Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2, Groups A, B, C, D</li><li>• Class I, Zone 2, Groups IIC, IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
---------------------	---

### Logistics

Carton Quantity	1
-----------------	---

### Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL\\_MBF39x-R5](#)
- [Specifications - MBF391R5GX3 Specification Sheet English](#)
- [Specifications - MBF391-R5GX3 Specification Sheet French](#)
- [Specifications - MB Series Fluorescent Bi-Pin Specification Sheet](#)