



MBL101-GX2

Par Killark

No de catalogue [MBL101-GX2](#)

100W HPS Fluorescent 120V 3/4" Montage au plafond.



Caractéristiques

- Ballast tank and splice box – corrosion resistant copper-free aluminum alloy
- Baked powder epoxy/polyester finish, electrostatically applied for complete, uniform corrosion protection
- All external hardware – stainless steel
- Guard – copper-free aluminum alloy
- Normally shipped as components for quick delivery
- Refractor guard – steel with corrosion resistant finish
- Reflector – lightweight, corrosion resistant fiberglass reinforced polyester
- Fluorescent models furnished with lamps.
- Energy efficient instant on white light (2700K). 10,000 hour lamp life
- HID lamp holders are E26 medium base

Général

Catalog Number	MBL101-GX2
Indicateur EU RoHs	Contact Manufacturer
Matériau	Aluminum, Copper Free (less than 4/10 of 1%)
Source d'éclairage	High Pressure Sodium
Série	MB
Type d'ampoule	Medium Base
Type d'élément optique	Glass Globe - Fluted
Type de fini	Powder Epoxy Paint
Type de montage	Ceiling
UPC	783936993751

Dimensions

Taille du moyeu 3/4"

Caractéristiques électriques

Fréquence nominale 60 Hz
Puissance en Watts 100 W
Tension nominale 120 VAC

Certifications et conformité

Classement(s) de risque

- Class I, Division 2, Groups A, B, C, D
- Class I, Zone 2, Groups IIC, IIB, IIA
- Class II, Divisions 1 & 2, Groups E, F, G
- Class III, Divisions 1 & 2

Logistique

Quantité dans l'emballage 1

Documentation

[Customer Notices - Prop 65 Notice](#)
[Photometry - KIL_MBL10x-G](#)
[Photometry - KIL_MBL10x-G-A](#)
[Photometry - KIL_MBL10x-G-S](#)



Une marque Hubbell

©2024 Hubbell Incorporated. Tous droits réservés
KILL_CA-MBL101GX2-SPEC-FR | REV 7/2024