



MBL701-GGB2 NR - 70W HPS Fluorescent 120V 3/4" Wall Mount with Globe and Guard- Ex nR

By Killark
Catalog # [MBL701-GGB2 NR](#)

70W HPS Fluorescent 120V 3/4" Wall Mount with Globe and Guard- Ex nR

Features

-
-
-
-
-
-
-
-
-
-

General

Catalog Number	MBL701-GGB2 NR
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Medium Base
Light Source	High Pressure Sodium
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Wall Bracket
Optic Type	Glass Globe - Fluted
Series	MB
UPC	783936044774

Dimensions



Hub Size3/4"

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	120 VAC
Wattage	70 W

Certifications And Compliance

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
---------------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_MBL70x-G-S](#)
- [Photometry - KIL_MBL70x-G-A](#)
- [Photometry - KIL_MBL70x-G](#)
- [Specifications - MB Series Fluorescent Bi-Pin Specification Sheet](#)
- [Specifications - MBL701-GGB2 NR Specification Sheet French](#)
- [Specifications - MBL701GGB2NR Specification Sheet English](#)