



MC2X6 - MC2X Series - Aluminum Cable Connector 2" NPT Resin Barrier

By Killark
Catalog # [MC2X6](#)



MC2X Series - Aluminum Cable Connector 2" NPT Resin Barrier.

Features

- Red anodized back-nut with hand grip tightening mechanism for ease of installation
- 360° stainless steel reusable ground spring
- Allows for Hawke Express & CELOX 's self-mixing two part epoxy resin for fast curing barrier seal to reduce cable installation time
- Patent pending damming solution for superior barrier seal
- Copper-free aluminum construction for harsh and corrosive atmospheres
- New design allows for Type 3, 4X, 6 ratings along with IP66 and IPx8 protection
- For use with armored and unarmored cable types
- Traditional hand-mix putty epoxy comes standard

General

Finish Type	Natural
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	MC2X
Type	<ul style="list-style-type: none">• Cable Gland• Cable Gland
UPC	783936179827

Dimensions

Hub Size 2"

Conductor Related

Cable Range 1.47 - 2.04 in

Product Assets

- [3D Models - MC2X6 3D Model \(STP\)](#)
- [3D Product View](#)
- [Brochures - MC2X Brochure](#)
- [Certifications - MC2X, MC, MCX, & TCX Series Cable Glands CSA Certification](#)
- [Installation Manuals - MC2X Series Cable Glands IOM K1300](#)
- [Video - MC2X Product Video](#)

Related Products

- [MCX19C](#)
- [MCX29](#)
- [MC14C](#)
- [MC19C](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
KILL_CA-MC2X6-SPEC-EN | REV 1/2024