

## MC4 - MC Series - Aluminum Cable Connector 1-1/4" NPT

By Killark  
Catalog # [MC4](#)

MC Series - Aluminum Cable Connector 1-1/4" NPT



\*Representative Image

### Features

- 
- 
- 
- 

### Application

Designed for use with jacketed interlocked, continuously corrugated and welded armor cable. Install where it is essential to provide positive grounding to the cable and for a Type 3, 4 connection.

### General

Catalog Number	MC4
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	MC
Temperature Rating	-50°C to +60°C
Type	Cable Gland
UPC	783936960623

### Dimensions

Dimensions	4 in x 3 in x 3 in
Gross Weight with Packaging	0.44
Height	3 in
Hub Size	1-1/4"
Length	4 in
Width	3 in

### Conductor Related

Cable Range	1.23 - 1.56 in
-------------	----------------

### Product Assets

Brochures - MC/MCX Series Brochure
Certifications - MC2X, MC, MCX, & TCX Series Cable Glands CSA Certification
Customer Notices - Prop 65 Notice
Installation Manuals - MC Series Cable Glands IOM K1405
SDS - LT Comp Resin SDS
SDS - LT Comp Hardner SDS
Specifications - MC4 Specification Sheet English
Specifications - MC4 Specification Sheet French
Specifications - MC Series Specification Sheet