



MOC-6M-WR - MO Series - Iron Mogul Conduit Body With Cover, Gasket, And Built-In Cable Rollers - C Type - Hub Size 2 Inch - Volume 144.0 Cubic Inches

By Killark
Catalog # [MOC-6M-WR](#)



*Representative Image

MO Series - Iron Mogul Conduit Body With Cover, Gasket, And Built-In Cable Rollers - C Type - Hub Size 2 Inch - Volume 144.0 Cubic Inches

Application

Mogul fittings are for use with rigid and IMC raceways. Use where standard conduit bodies do not provide adequate access and wiring area for the pulling of large and heavy conductors. For right angle bends where splices, pulls, and taps are needed in a we

General

Catalog Number	MOC-6M-WR
Color	Glossy gray
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	C
Material	Iron
Series	Moguls
Type	Mogul Conduit Body With Cover, Gasket, & Cable Rollers
UPC	783936555102

Dimensions

Dimensions	19 in x 4 in x 4 in
Gross Weight with Packaging	21.5
Height	4 in
Hub Size	2"
Length	19 in
Width	4 in

Product Assets

- [Certifications - MOGUL Series Fitting CSA Certificate of Compliance](#)
- [Certifications - MOGUL Series Fitting UL Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - MOC-6M-WR Specification Sheet French](#)
- [Specifications - MOC6MWR Specification Sheet English](#)
- [Specifications - MO Series Mogul Conduit Bodies Specification Sheet](#)