



NV2FG32BSG - 32W 120-277V Fluorescent Wall Mount with Standard Globe and Guard

By Killark
Catalog # [NV2FG32BSG](#)

32W 120-277V Fluorescent Wall Mount with Standard Globe and Guard.

Features

- NV2 Series non-metallic light fixtures combine an outstanding balance of strength, stiffness, toughness and electrical properties
- Energy and labor saving fluorescent or incandescent models
- Accessories include polycarbonate dome reflectors and wall extension
- Molded from 30% glass-filled thermoset polyester for high strength
- Resists corrosive effects of most chemicals, hydrocarbons and solvents
- Designed for indoor and outdoor, globe down applications.

General

Catalog Number	NV2FG32BSG
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Lamp Type	Bi Pin
Light Source	
Material	Polyester, Fiberglass Reinforced
Mounting Type	
Optic Type	Glass Globe - Clear
Series	NV
UPC	783936050843

Dimensions

Hub Size	3/4"
----------	------

Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	120-277 VAC
Wattage	32 W



Certifications And Compliance

Hazardous Rating(s)	Class I, Division 2, Groups A, B, C, D Class I, Zone 2, Groups IIC, IIB, IIA Class II, Division 2, Groups F, G Class III, Divisions 1 & 2
---------------------	--

Product Assets

[Certifications - NV2 Series CSA Certification](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - NV2 Series IOM K1301](#)
[Photometry - KIL_NV2FG32xSG](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-NV2FG32BSG-SPEC-EN | REV 6/2024