

# KILLARK®

## NV2FG42BHG

By Killark  
Catalog # [NV2FG42BHG](#)

42W 120-277V Fluorescent Wall Mount with Tempered Globe and Guard.



### Features

- NV2 Series non-metallic light fixtures combine an outstanding balance of strength, stiffness, toughness and electrical properties
- Energy and labor saving fluorescent or incandescent models
- Accessories include polycarbonate dome reflectors and wall extension
- Molded from 30% glass-filled thermoset polyester for high strength
- Resists corrosive effects of most chemicals, hydrocarbons and solvents
- Designed for indoor and outdoor, globe down applications.

### General

Finish Type	Peinture époxy en poudre
Lamp Type	Bi Pin
Light Source	Compact Fluorescent
Material	Polyester, Fiberglass Reinforced
Mounting Type	Wall Bracket
Optic Type	Glass Globe - Clear
Series	NV
UPC	783936050911

### Dimensions

Hub Size 3/4"

### Electrical Ratings

Frequency Rating 50/60 Hz  
Voltage Rating 120-277 VAC  
Wattage 42 W

### Certifications and Compliance

- Hazardous Rating(s)
- Class I, Division 2, Groups A, B, C, D
  - Class I, Zone 2, Groups IIC, IIB, IIA
  - Class II, Division 2, Groups F, G
  - Class III, Divisions 1 & 2

### Product Assets

[Certifications - NV2 Series CSA Certification](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - NV2 Series IOM K1301](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
KILL\_CA-NV2FG42BHG-SPEC-EN | REV 1/2024