



NV2IG15XSG

By Killark
Catalog # [NV2IG15XSG](#)

150W Incandescent Ceiling Mount with Standard Globe and Guard.



Features

- NV2 Series non-metallic light fixtures combine an outstanding balance of strength, stiffness, toughness and electrical properties
- Energy and labor saving fluorescent or incandescent models
- Accessories include polycarbonate dome reflectors and wall extension
- Molded from 30% glass-filled thermoset polyester for high strength
- Resists corrosive effects of most chemicals, hydrocarbons and solvents
- Designed for indoor and outdoor, globe down applications.

General

Finish Type	Peinture époxy en poudre
Lamp Type	Medium Base
Light Source	Incandescent
Material	Polyester, Fiberglass Reinforced
Mounting Type	Ceiling
Optic Type	Glass Globe - Clear
Series	NV
UPC	783936050584

Dimensions

Hub Size 3/4"

Electrical Ratings

Frequency Rating 50/60 Hz
Voltage Rating 120-277 VAC
Wattage 150 W

Certifications and Compliance

- Hazardous Rating(s)
- Class I, Division 2, Groups A, B, C, D
 - Class I, Zone 2, Groups IIC, IIB, IIA
 - Class II, Division 2, Groups F, G
 - Class III, Divisions 1 & 2

Product Assets

[Certifications - NV2 Series CSA Certification](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - NV2 Series IOM K1301](#)
[Photometry - KIL_NV2IG15xSG](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
KILL_CA-NV2IG15XSG-SPEC-EN | REV 1/2024